

Remote Blower Performance Testing

Blower Tested - Part Number # 4863500

Static Pressure (Inches of Water)	Air Velocity (FPM)	Air Volume (CFM)
* .1302	920	540
.2043	885	520
.3071	845	496
.4075	805	473
.5050	745	437
.6066	685	402
.6933	615	361

Notes: Blower connected to 10' PVC duct for test (Actual O.D. 10.75" - Actual I.D. 10.375")

* Damper Full Open

Motor ¼ HP

RPM 1725

Voltage 115 V

Frequency 60 Hz

Current 4.4 Amps

